Home | Optics | Telecentric lenses | TC1MHR-TC4MHR series | TC4MHR064-C

# OPTO ENGINEERING

## TC4MHR064-C

High resolution telecentric lens for 4/3" detectors, magnification 0.275x, C-mount

#### **SPECIFICATIONS**

Magnification	(x)	0.275
Image circle Ø	(mm)	21.6
Object field of view 8	(mn	n x mm or Ø)
with IMX174/IMX249 13.3 mm diag w x h 11.35 x 7.13		41.25 x 25.91
with IMX255/IMX267 16.1 mm diag w x h 14.19 x 7.51		51.60 x 27.31
with IMX253/IMX304 17.6 mm diag w x h 14.16 x 10.37 51.49		51.49 x 37.71
with KAI-4022/4021 21.5 mm diagonal w x h 15.2 x 15.2 55.3 x 55.		55.3 x 55.3
with KAI-08050 22.6 mm diagonal w x h 18.1 x 13.6(7) 65.8 x 4		65.8 x 49.5





#### Optical specifications

Working distance (1)	(mm)	181.9
wF/# (2)		16
Telecentricity typical (max) (3)	(deg)	<0.05 (0.10)
Distortion typical (max) (4)	(%)	<0.04 (0.10)
Field depth (5)	(mm)	15.9
CTF@ 50 lp/mm	(%)	> 40

Mechanical specifications		
Mount		С
Phase adjustment(9)		Yes
Length (6)	(mm)	301.8
Diameter	(mm)	100
Mass	(g)	1149
Last undata, 2010 OC 12		

Last update: 2018-06-12

#### NOTES

- 1. Working distance: distance between the front end of the mechanics and the object. Set this distance within +/- 3% of the nominal value for maximum resolution and minimum distortion.
- 2. Working F-number (wF/#): the real F-number of a lens when used as a macro. Lenses with smaller apertures can be supplied on request.
- Maximum slope of chief rays inside the lens: when converted to milliradians, it gives the maximum
  measurement error for any millimeter of object displacement. Typical (average production) values and
  maximum (guaranteed) values are listed.
- 4. Percent deviation of the real image compared to an ideal, undistorted image: typical (average production) values and maximum (guaranteed) values are listed.
- 5. At the borders of the field depth the image can be still used for measurement but, to get a perfectly sharp image, only half of the nominal field depth should be considered. Pixel size used for calculation is 5 µm.
- 6. Measured from the front end of the mechanics to the camera flange.
- 7. With KAI-08050 (22.6 mm diagonal) detectors, the FOV of TC4MHRyyy-x lenses may show some vignetting at the image corners.
- 8. For the fields with the indication "Ø =", the image of a circular object of such diameter is fully inscribed into the detector.

#### COMPATIBLE PRODUCTS

Despite the efforts made to generate an error-free compatibility list, we always recommend to consult the Opto Engineering® technical support department before purchasing a compatible product. Opto Engineering® shall not be liable for any damage or malfunctioning caused by the incorrect selection of a compatible product.




LTCLHP series

High-performance telecentric illuminators

LTCLHP064-R	Telecentric HP illuminator, beam diameter 80 mm, red
LTCLHP064-G	Telecentric HP illuminator, beam diameter 80 mm, green

All product specifications and data are subject to change without notice to improve reliability, functionality, design or other. Photos and pictures are for illustration purposes only.





#### LTCLHP CORE series

Ultra compact telecentric illuminators

LTCLCR064-R	Telecentric CORE illuminator, beam dimensions $\emptyset$ = 86; x = 67, red
LTCLCR064-G	Telecentric CORE illuminator, beam dimensions Ø = 86; x = 67, green
LTCLCR064-W	Telecentric CORE illuminator, beam dimensions Ø = 86; x = 67, white



#### LTLA series

 $\label{thm:linear} \mbox{High-power strobed LED low angle diffused ringlights}$ 

LTLAC1-W	Diffusive strobed low angle ring light illuminator - large size medium power white
LTLAC2-R	Diffusive strobed low angle ring light illuminator - large size high power red
LTLAC2-G	Diffusive strobed low angle ring light illuminator - large size high power green
LTLAC2-W	Diffusive strobed low angle ring light illuminator - large size high power white



LTLAIC series (discontinued models)

Continuous LED low angle diffused ringlights

LT2RZF120-60-2-W-24V	LED ringlight, 2 LED rows, 126.5 mm outer diameter, 60°, white, 24V
LT2RZF120-60-2-R-24V	LED ringlight, 2 LED rows, 126.5 mm outer diameter, 60°, red, 24V
LT2RZF120-60-2-G-24V	LED ringlight, 2 LED rows, 126.5 mm outer diameter, 60°, green, 24V
LT2RZF120-60-2-B-24V	LED ringlight, 2 LED rows, 126.5 mm outer diameter, 60°, blue, 24V



#### LTLAIC series

Continuous LED low angle diffused ringlights

LT3RZF130-60-1-W-24V	LED ringlight, 1 LED row, 131.5 mm outer diameter, 60°, white, 24V
LT3RZF130-60-1-R-24V	LED ringlight, 1 LED row, 131.5 mm outer diameter, 60°, red, 24V
LT3RZF130-60-1-G-24V	LED ringlight, 1 LED row, 131.5 mm outer diameter, 60°, green, 24V
LT3RZF130-60-1-B-24V	LED ringlight, 1 LED row, 131.5 mm outer diameter, 60°, blue, 24V



### LTLADC series

Continuous LED low angle direct ringlights

LTZZO130-75-3-W-24V	LED low angle ringlight, 3 LED rows, outer diameter 131 mm, 75°, white, 24V
LTZZO130-75-3-R-24V	LED low angle ringlight, 3 LED rows, outer diameter 131 mm, 75°, red, 24V
LTZZO130-75-3-G-24V	LED low angle ringlight, 3 LED rows, outer diameter 131 mm, 75°, green, 24V
LTZZO130-75-3-B-24V	LED low angle ringlight, 3 LED rows, outer diameter 131 mm, 75°, blue, 24V



#### LTRNST series

LED ring illuminators - straight type

LTRN064RD	Ring LED illuminator, inner diameter 100 mm, straight type, red 630 nm
LTRN064GR	Ring LED illuminator, inner diameter 100 mm, straight type, green 525 nm
LTRN064BL	Ring LED illuminator, inner diameter 100 mm, straight type, blue 470 nm
LTRN064NW	Ring LED illuminator, inner diameter 100 mm, straight type, white



#### LTBC series

Continuos LED backlight

LTBC114114-W	Continuos LED backlight, 114x114 illumination area, white
LTBC114114-G	Continuos LED backlight, 114x114 illumination area, green



#### LTBFC series

Continuous flat side-emitting LED backlights

LTPVR100-00-1-R-24V	Flat side-emitting LED backlight, 100X100 mm illumination area, red, 24V
LTPVR100-00-1-G-24V	Flat side-emitting LED backlight, 100X100 mm illumination area, green, 24V
LTPVR100-00-1-B-24V	Flat side-emitting LED backlight, 100X100 mm illumination area, blue, 24V



LTBRDC series

#### Continuous LED bar lights

LTZPFL120-00-6-W-24V	LED bar light, 6 LED rows, 120X26.3 illumination area, white, 24V
LTZPFL120-00-6-R-24V	LED bar light, 6 LED rows, 120X26.3 illumination area, red, 24V
LTZPFL120-00-6-G-24V	LED bar light, 6 LED rows, 120X26.3 illumination area, green, 24V
LTZPFL120-00-6-B-24V	LED bar light, 6 LED rows, 120X26.3 illumination area, blue, 24V



LTCXC series

#### Continuous LED coaxial lights

LT2QOG100-00-X-W-24V	LED coaxial light, 100x100 mm light emitting area, white, 24V
LT2QOG100-00-X-R-24V	LED coaxial light, 100x100 mm light emitting area, red, 24V
LT2QOG100-00-X-G-24V	LED coaxial light, 100x100 mm light emitting area, green, 24V
LT2QOG100-00-X-B-24V	LED coaxial light, 100x100 mm light emitting area, blue, 24V



CMBS series

45° beam splitters

CMBS064

 $45^{\circ}$  beam splitter with mount for 100 mm clamping diameter optics



CMMR series

45° first surface mirrors

CMMR064

 $45^{\circ}$  first surface mirror for 100 mm clamping diameter optics





WI series

Protective windows

WI064

Protective window for 100 mm clamping diameter optics



CMHO series

Clamping mechanics

CMHO064

Clamping mechanics for TCxx064 lenses and LTCLHP064-X illuminators



Accessories

Accessories and add-ons to make the most of Opto Engineering lenses.

т	11.7	т	п	г
н	L	ш	ы	н
	FI	FIL	FILT	FILTE

Filter mount for telecentric lenses



Precision alignment mechanics

CMTH064

Precision alignment mechanics for telecentric optics 064



mvBlueFOX3-2 series

USB3 vision camera with Sony Pregius CMOS sensors

RT-mvBF3-2089a	USB3 Vision camera with Sony Pregius CMOS sensor IMX267
RT-mvBF3-2089	USB3 Vision camera with Sony Pregius CMOS sensor IMX255
RT-mvBF3-2124a	USB3 Vision camera with Sony Pregius CMOS sensor IMX304
RT-mvBF3-2124	USB3 Vision camera with Sony Pregius CMOS sensor IMX253



mvBlueCOUGAR series

RT-mvBC-X109b	Camera with interface GigE (1GB/s), sensor size 1", mpixel 8.95, resolution 4112 x 2176, sensor name IMX267, sensor type CMOS
RT-mvBC-XD109b	Camera with interface Dual GigE (2GB/s), sensor size 1", mpixel 8.95, resolution 4112 X 2176, sensor name IMX267, sensor type CMOS
RT-mvBC-X1012b	Camera with interface GigE (1GB/s), sensor size 1.1", mpixel 12.37, resolution 411 x 3008, sensor name IMX304, sensor type CMOS
RT-mvBC-XD107	Camera with interface Dual GigE (2GB/s), sensor size 1.1", mpixel 7.1, resolution 3216 x 2208, sensor name IMX420, sensor type CMOS
RT-mvBC-XD1012b	Camera with interface Dual GigE (2GB/s), sensor size 1.1", mpixel 12.37, resolution 4112 x 3008, sensor name IMX304, sensor type CMOS



20MP, 26MP and 29MP area scan cameras for high-speed applications

COE-200-M-POE-070-IR-C	HR Area Scan camera IMX183, CMOS, Rolling shutter, 5472 $\times$ 3648, 20.4 MP, 2.4 pix, 1", Gray, GigE, 6 fps, POE, C - mount, Glass filter
COE-200-C-POE-070-IR-C	HR Area Scan camera IMX183, CMOS, Rolling shutter, 5472 $\times$ 3648, 20.4 MP, 2.4 pix, 1", Color, GigE, 6 fps, POE, C - mount, Infrared cut filter
COE-200-M-USB-070-IR-C	HR Area Scan camera IMX183, CMOS, Rolling shutter, 5472 × 3648, 20.4 MP, 2.4 pix, 1", Gray, 14 fps, C - mount, Glass filter
COE-200-C-USB-070-IR-C	HR Area Scan camera IMX183, CMOS, Rolling shutter, 5472 × 3648, 20.4 MP, 2.4 pix, 1", Color, 14 fps, C - mount, Infrared cut filter